



## Trunking 12x20, L=2,1m, brown

Product Datasheet

### Architecture

|             |                |
|-------------|----------------|
| Fixing mode | bottom punched |
|-------------|----------------|

### Functions

|  |    |
|--|----|
| Suitable for functional integrity according to DIN 4102-12 | no |
|--|----|

### Configuration

|                         |    |
|-------------------------|----|
| Antibacterial treatment | no |
|-------------------------|----|

### Connectivity

|                   |                 |
|-------------------|-----------------|
| Trunking coupling | without coupler |
|-------------------|-----------------|

### Cover, door

|           |            |
|-----------|------------|
| Lid shape | premounted |
|-----------|------------|

### Materials

|                           |                        |
|---------------------------|------------------------|
| Colour                    | brown                  |
| RAL colour                | RAL 8014 - Sepia brown |
| Material                  | PVC                    |
| Material group            | plastic                |
| Type of surface treatment | untreated              |
| Transparent               | no                     |

### Dimensions

|                 |         |
|-----------------|---------|
| Trunking height | 13 mm   |
| Length          | 2100 mm |
| Trunking width  | 24 mm   |

### Cable

|  |                     |
|--|---------------------|
| Number of wires 1,5 mm <sup>2</sup> - 40% filling degree | 14                  |
| Internal/useful cross section                            | 240 mm <sup>2</sup> |
| Number of wires 2,5 mm <sup>2</sup> - 40% filling degree | 10                  |

### Scope of delivery

|                  |    |
|------------------|----|
| Delivery on roll | no |
|------------------|----|

### Equipment

|                             |    |
|-----------------------------|----|
| Number of fix dividers      | 1  |
| Cable retainers per meter   | 4  |
| Cable fixing clips included | no |
| With protective film        | no |

ATA122018014

## Standards

|                         |                      |
|-------------------------|----------------------|
| Approvals               | EN50085-2-1          |
| European directive RoHs | voluntary compliance |

## Safety

|                     |      |
|---------------------|------|
| Protection index IP | IP40 |
| Halogen free        | no   |
| Impact strength     | IK07 |

## Use conditions

|                       |            |
|-----------------------|------------|
| Operating temperature | -5...65 °C |
|-----------------------|------------|