



Internal corner, ATEHA 12x20, brown

Product Datasheet

Architecture

Fixing mode	Clipped
-------------	---------

Functions

Overlapping	yes
-------------	-----

Suitable for functional integrity according to DIN 4102-12	no
--	----

Configuration

Antibacterial treatment	no
-------------------------	----

Symetrical	yes
------------	-----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Cover, door

Lid with softlip	No
------------------	----

Materials

Colour	brown
--------	-------

RAL colour	RAL 8014 - Sepia brown
------------	------------------------

Material	ABS
----------	-----

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

Dimensions

Trunking height	12 mm
-----------------	-------

Length	48 mm
--------	-------

Trunking width	20 mm
----------------	-------

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	83 / 140 °
-------------	------------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Equipment

Cable fixing clips included	yes
-----------------------------	-----

With protective film	no
----------------------	----

ATA122048014

Standards

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP40
Halogen free	yes
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...60 °C
---------------------	------------