



ATA123048014

## Internal corner, ATEHA, 12x30, brown

Product Datasheet

### Architecture

|             |         |
|-------------|---------|
| Fixing mode | Clipped |
|-------------|---------|

### Functions

|  |     |
|--|-----|
| Overlapping  | yes |
| Suitable for functional integrity according to DIN 4102-12 | no  |

### Configuration

|                         |     |
|-------------------------|-----|
| Antibacterial treatment | no  |
| Symmetrical             | yes |

### Connectivity

|                   |                 |
|-------------------|-----------------|
| Trunking coupling | without coupler |
|-------------------|-----------------|

### Cover, door

|                  |    |
|------------------|----|
| Lid with softlip | No |
|------------------|----|

### Materials

|                           |                        |
|---------------------------|------------------------|
| Colour                    | brown                  |
| RAL colour                | RAL 8014 - Sepia brown |
| Material                  | ABS                    |
| Material group            | plastic                |
| Type of surface treatment | untreated              |

### Dimensions

|                 |       |
|-----------------|-------|
| Trunking height | 12 mm |
| Length          | 48 mm |
| Trunking width  | 30 mm |

### Installation, mounting

|               |                       |
|---------------|-----------------------|
| Base punching | Without base punching |
|---------------|-----------------------|

### Settings

|             |            |
|-------------|------------|
| Angle range | 83 / 140 ° |
|-------------|------------|

### Accessories included

|                         |         |
|-------------------------|---------|
| Accessory configuration | Moulded |
|-------------------------|---------|

### Equipment

|                             |     |
|-----------------------------|-----|
| Cable fixing clips included | yes |
| With protective film        | no  |

## Standards

|                         |                      |
|-------------------------|----------------------|
| Approvals               | EN50085-2-1          |
| European directive RoHs | voluntary compliance |

## Safety

|                     |      |
|---------------------|------|
| Protection index IP | IP40 |
| Halogen free        | yes  |
| Impact strength     | IK07 |

## Use conditions

|                       |            |
|-----------------------|------------|
| Operating temperature | -5...60 °C |
|-----------------------|------------|

## temperatur

|                     |            |
|---------------------|------------|
| Ambient temperature | -5...60 °C |
|---------------------|------------|