



## Trunking 16x30, L=2,1m, pure white

Product Datasheet

### Architecture

Fixing mode	bottom punched
-------------	----------------

### Functions

Suitable for functional integrity according to DIN 4102-12	no
--	----

### Configuration

Antibacterial treatment	no
-------------------------	----

### Connectivity

Trunking coupling	without coupler
-------------------	-----------------

### Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	2
Maximum number of cables (Ø 11 mm, 50% fill)	3

### Cover, door

Lid shape	premounted
-----------	------------

### Materials

Colour	pure white
RAL colour	RAL 9010 - Pure white
Material	PVC
Material group	plastic
Type of surface treatment	untreated
Transparent	no

### Dimensions

Trunking height	16 mm
Length	2100 mm
Trunking width	32 mm

### Installation, mounting

Base punching	Without base punching
---------------	-----------------------

### Cable

Number of wires 1,5 mm <sup>2</sup> - 40% filling degree	32
Internal/useful cross section	420 mm <sup>2</sup>
Number of wires 2,5 mm <sup>2</sup> - 40% filling degree	26

### Scope of delivery

Delivery on roll	no
------------------	----

ATA163009010



## Equipment

Compartment quantity	1
Cable retainers per meter	2
Cable fixing clips included	yes
With protective film	no

## Standards

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

## Safety

Protection index IP	IP40
Halogen free	no
Impact strength	IK07

## Use conditions

Operating temperature	-5...65 °C
-----------------------	------------