



SL201159609010

**acc.box SL20115 2 x gang (Fr) pw**

Product Datasheet

**Architecture**

Connection system	Other
Fixing mode	Clamping and screwable

**Configuration**

Antibacterial treatment	no
Empty housing	no

**Compatibility**

Device installation compatible format	45x45 mm
---------------------------------------	----------

**Main electrical features**

Nominal voltage	230 V
-----------------	-------

**Materials**

Colour	pure white
RAL colour	RAL 9010 - Pure white
Material	Mixed materials
Material group	mixed material

**Dimensions**

Trunking height	115 mm
Trunking width	20 mm
Format	overhanging wiring accessory

**Installation, mounting**

Mounting way	horizontal
--------------	------------

**Accessories included**

Fitted with	socket outlet
-------------	---------------

**Equipment**

Number of units	2
-----------------	---

**Standards**

Approvals	CE
European directive RoHs	voluntary compliance

**Safety**

Protection index IP	IP40
Halogen free	yes
Impact strength	IK07

**Use conditions**

Operating temperature	5...60 °C
-----------------------	-----------

**temperatur**

Ambient temperature	5...60 °C
---------------------	-----------

**Identification**

Version	F
---------	---