



Liféa trunking30x57coupling, 2cable r., g

Product Datasheet

Architecture

Fixing mode bottom punched

Functions

Suitable for functional integrity according to DIN 4102-12 no

Configuration

Antibacterial treatment no

Connectivity

Trunking coupling Pre-equipped with couplers

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 6

Cover, door

Lid shape loose

Materials

Colour stone grey

RAL colour RAL 7030 - Stone grey

Material PVC

Material group plastic

Type of surface treatment untreated

Transparent no

Dimensions

Trunking height 30 mm

Length 2000 mm

Trunking width 57 mm

Distance bottom-punch along trunking-direction 125 mm

Distance bottom-punch crosswise trunking-direction 18 mm

Cable

Internal/useful cross section 1250 mm²

Scope of delivery

Delivery on roll no

Equipment

Cable retainers per meter 2

Cable fixing clips included no

With protective film no

LFF3006007030

Standards

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP40
Halogen free	no
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------
