



ATA207528014

Trunking 20x75, L=2,0m, brown

Product Datasheet

Architecture

Fixing mode bottom punched

Functions

Suitable for functional integrity according to DIN 4102-12 no

Configuration

Antibacterial treatment no

Connectivity

Trunking coupling without coupler

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 7
Maximum number of cables (Ø 11 mm, 50% fill) 7

Cover, door

Lid shape premounted

Materials

Colour brown
RAL colour RAL 8014 - Sepia brown
Material PVC
Material group plastic
Type of surface treatment untreated
Transparent no

Dimensions

Trunking height 20 mm
Length 2000 mm
Trunking width 74 mm

Cable

Number of wires 1,5 mm² - 40% filling degree 89
Internal/useful cross section 1296 mm²
Number of wires 2,5 mm² - 40% filling degree 71

Scope of delivery

Delivery on roll no

Equipment

Number of fix dividers	2
Cable retainers per meter	2
Cable fixing clips included	yes
With protective film	no

Standards

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP40
Halogen free	no
Impact strength	IK07

Use conditions

Operating temperature	-5 ... 65 °C
-----------------------	--------------