



SL200559609010

acc.box SL20055 2 x gang (Fr) pw

Product Datasheet

Architecture

Connection system	Other
Fixing mode	Clamping and screwable

Configuration

Antibacterial treatment	no
Empty housing	no

Compatibility

Device installation compatible format	45x45 mm
---------------------------------------	----------

Main electrical features

Nominal voltage	230 V
-----------------	-------

Materials

Colour	pure white
RAL colour	RAL 9010 - Pure white
Material	Mixed materials
Material group	mixed material

Dimensions

Trunking height	55 mm
Trunking width	20 mm
Format	overhanging wiring accessory

Installation, mounting

Assembly	modular
Mounting way	horizontal

Accessories included

Fitted with	socket outlet
-------------	---------------

Equipment

Number of units	2
-----------------	---

Standards

Approvals	CE
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP40
Halogen free	yes
Impact strength	IK07

Use conditions	
Operating temperature	5...60 °C
temperatur	
Ambient temperature	5...60 °C
Identification	
Version	F