



Trunking base SL200801 black

Product Datasheet

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	6
Cable capacity 11mm D e.g. NYM 3 x 1.5mm ² 2nd chamber	2 Part
Cable capacity 11mm D e.g. NYM 3 x 1.5mm ² 3rd chamber	4 Part

Materials

Colour	black
Material	PVC
Material group	plastic
Type of surface treatment	Other

Dimensions

Trunking height	80 mm
Length	2000 mm
Trunking width	20 mm

Cable

Number of wires 1,5 mm ² - 40% filling degree	72
Number of wires 2,5 mm ² - 40% filling degree	46

Equipment

Number of fix dividers	2
Compartment quantity	3
With carpet border	no
With protective film	no

Standards

Approvals	CE
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP40
Halogen free	no
Impact strength	IK07

Use conditions

Operating temperature	5...60 °C
-----------------------	-----------

temperatur

Ambient temperature	5...60 °C
---------------------	-----------

SL200801

