



HXE040H

Motor operator h800-h1000 24-48V DC

Product Datasheet

Architecture

Type of order	motor drive
---------------	-------------

Main electrical features

Type of supply voltage	DC
------------------------	----

Voltage

DC control voltage	24 / 48 V
Rated operational voltage in DC	24 / 48 V

Power

Total power loss under IN	24 W
---------------------------	------

Standards

European directive RoHS	voluntary compliance
European directive WEEE	concerned

Safety

Protection index IP	IP4X
---------------------	------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m