



HXF040H

Motor operator h1250-h1600 24V DC

Product Datasheet

Architecture

Type of order motor drive

Main electrical features

Type of supply voltage DC

Voltage

DC control voltage 24 V

Rated operational voltage in DC 24 V

Power

Total power loss under IN 24 W

Standards

European directive RoHs voluntary compliance

European directive WEEE concerned

Safety

Protection index IP IP4X

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2 3

Altitude 2000 m