



FL646A

Poly. inner do. Orion+ 650x400 mm

Product Datasheet

Architecture

Fixing mode	Screw mounting
-------------	----------------

Configuration

Version as door for disconnecting switch interlocking	yes
---	-----

Cover, door

Type of door closing	Double lock bar 3mm
Door type for switch gear cabinet	Inner door
Door quantity	1
With cut out	no

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	glas reeinforced polyester
Surface appearance	mat
Type of surface treatment	untreated

Dimensions

Depth of installed product	20 mm
Height of installed product	600 mm
Width of installed product	350 mm

Equipment

Number of keys	2
----------------	---

Standards

Approvals	CE
European directive WEEE	not concerned

Safety

Protection index IP	IP30
Protection class	isol.class II
Halogen free	yes