



acc.box coupling SL20080 purewhite

Product Datasheet

Architecture

| | |
|-------------|---------|
| Fixing mode | Clipped |
|-------------|---------|

Functions

| | |
|-------------|-----|
| Overlapping | yes |
|-------------|-----|

Configuration

| | |
|-------------------------|----|
| Antibacterial treatment | no |
|-------------------------|----|

Materials

| | |
|---------------------------|-----------------------|
| Colour | pure white |
| RAL colour | RAL 9010 - Pure white |
| Material | ABS |
| Material group | plastic |
| Type of surface treatment | untreated |

Dimensions

| | |
|-----------------------------|--------|
| Height of installed product | 33 mm |
| Trunking height | 80 mm |
| Length | 110 mm |
| Trunking width | 20 mm |

Installation, mounting

| | |
|--------------|------------|
| Mounting way | horizontal |
|--------------|------------|

Equipment

| | |
|----------------------|----|
| With protective film | no |
|----------------------|----|

Standards

| | |
|-------------------------|----------------------|
| Approvals | CE |
| European directive RoHs | voluntary compliance |

Safety

| | |
|---------------------|------|
| Protection index IP | IP40 |
| Halogen free | yes |
| Impact strength | IK07 |

Use conditions

| | |
|-----------------------|-----------|
| Operating temperature | 5...60 °C |
|-----------------------|-----------|

temperatur

| | |
|---------------------|-----------|
| Ambient temperature | 5...60 °C |
|---------------------|-----------|

SL20080A9010

