



G4731

## Connection 2000mm, Schuko-angle-plug

Product Datasheet

### Architecture

Connection system	Wago Winsta
-------------------	-------------

### Connectivity

Number of wires	3
-----------------	---

### Main electrical features

Nominal voltage	230 V
-----------------	-------

### Electric current

Rated current	16 A
---------------	------

### Length

Total length	2 m
--------------	-----

### Power

Fire load	5510 kJ
-----------	---------

### Resistance

Continuity resistor	1000 $\mu\Omega$
---------------------	------------------

### Materials

Colour	black
--------	-------

Colour coding / contact insert	black
--------------------------------	-------

Colour housing	black
----------------	-------

Colour outer sheath	Black
---------------------	-------

Material group	other
----------------	-------

Type of surface treatment	coated
---------------------------	--------

### Dimensions

Length	2000 mm
--------	---------

### Connection

Cross section connection cable	1,5 mm <sup>2</sup>
--------------------------------	---------------------

Type of finished cable	Device connection cable
------------------------	-------------------------

### Cable

Wire cross-section	1,5 mm <sup>2</sup>
--------------------	---------------------

Cable permanent temperature-resistant to	70 °C
--	-------

Cable diameter	11 mm
----------------	-------

Conductor cross-section	1,5 mm <sup>2</sup>
-------------------------	---------------------

## Equipment

Type side 1	Bus
Mechanical coding	yes
Type side 2	Mains plug

## Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

## Safety

Protection index IP	IP20
Halogen free	no

## temperatur

Insulating piece permanent temperature-resistant	105 °C
--	--------