



G3155

## Data socket 2g, cat6 UTP, 8/8 pin

### Product Datasheet

#### Architecture

Fixing mode	Clamping and screwable
-------------	------------------------

#### Configuration

Module	2 Gang
--------	--------

#### Compatibility

Product compatibility	Geräteeinbau ECOLINE
Device installation compatible format	Standard 60mm

#### Connectivity

Direction of outlet (for data sockets copper)	angled
---	--------

#### Materials

Colour	not applicable
Material	Mixed materials
Material group	mixed material
Type of surface treatment	untreated

#### Dimensions

Length	70 mm
Format	Ecoline

#### Installation, mounting

Installation in floor-box or sub-floor-system	no
---	----

#### Connection

Type of connection	Insulation displacement connector
--------------------	-----------------------------------

#### Accessories included

Fitted with	data outlet
-------------	-------------

#### Equipment

With transparent product label holder	no
---------------------------------------	----

#### Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

#### Safety

Protection index IP	IP20
---------------------	------

#### Identification

Producer	BTR
Category	Cat6, 8 points