

module 4 outl.,3 outl. lckd, connect.Wago

Product Datasheet

Architecture

Connection system	Wago Winsta
-------------------	-------------

Functions

Overvoltage protection	no
------------------------	----

Main electrical features

Nominal voltage	250 V
Type of supply voltage	AC

Electric current

Rated current	16 A
---------------	------

Power

Power	max. 3680 W
-------	-------------

Materials

Colour	aluminium
Material	Aluminium
Material group	aluminium

Dimensions

Height of installed product	55 mm
Length	375 mm
Width of installed product	55 mm

Installation, mounting

Mounting type	surface
---------------	---------

Connection

Cross section connection cable	2,5 mm ²
--------------------------------	---------------------

Equipment

Number of connection cables	max. 2
Number of household socket outlets	4
Extension possible	no

Use

Folding	no
---------	----

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP20
Halogen free	yes

Shape

Shape	Square
-------	--------