

module 3 outlets, 2x22,5 empty

Product Datasheet

Functions

Overvoltage protection	no
------------------------	----

Main electrical features

Nominal voltage	250 V
-----------------	-------

Type of supply voltage	AC
------------------------	----

Electric current

Rated current	16 A
---------------	------

Power

Power	max. 3680 W
-------	-------------

Materials

Colour	aluminium
--------	-----------

Material	Aluminium
----------	-----------

Material group	aluminium
----------------	-----------

Dimensions

Height of installed product	55 mm
-----------------------------	-------

Length	240 mm
--------	--------

Width of installed product	55 mm
----------------------------	-------

Installation, mounting

Mounting type	surface
---------------	---------

Connection

Cross section connection cable	2,5 mm ²
--------------------------------	---------------------

Equipment

Number of connection cables	max. 1
-----------------------------	--------

Number of appliances to build in	2
----------------------------------	---

Number of household socket outlets	3
------------------------------------	---

Extension possible	yes
--------------------	-----

Use

Folding	no
---------	----

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP20
---------------------	------

Halogen free	yes
--------------	-----

Shape

Shape

Square