



G4741

**Connection 3000mm, Schuko-angle-plug**

Product Datasheet

**Architecture**

Connection system Wago Winsta

**Connectivity**

Number of wires 3

**Main electrical features**

Nominal voltage 230 V

**Electric current**

Rated current 16 A

**Length**

Total length 3 m

**Power**

Fire load 6947 kJ

**Resistance**

Continuity resistor 1000  $\mu\Omega$

**Materials**

Colour black

Colour coding / contact insert black

Colour housing black

Colour outer sheath Black

Material group other

Type of surface treatment coated

**Dimensions**

Length 3000 mm

**Connection**

Cross section connection cable 1,5 mm<sup>2</sup>

Type of finished cable Device connection cable

**Cable**

Wire cross-section 1,5 mm<sup>2</sup>

Cable permanent temperature-resistant to 70 °C

Cable diameter 11 mm

Conductor cross-section 1,5 mm<sup>2</sup>

## Equipment

Type side 1	Bus
Mechanical coding	yes
Type side 2	Mains plug

## Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

## Safety

Protection index IP	IP20
Halogen free	no

## temperatur

Insulating piece permanent temperature-resistant	105 °C
--	--------