



S165-22X

### Expert pet tolerant motion detector

Product Datasheet

#### Connectivity

Connection mode radio TwinBand

#### Voltage

Operating voltage 3 V

#### Measurement

Detection Method Passive Infrared

#### Battery

life of battery 4 years

#### Detection

Range of detection 12 m

#### Dimensions

Dimensions (LLxwxhh) 58 x 102 x 57 mm

#### Equipment

Angle of horizontal detection 85 °

#### Use

Lense type Pet-tolerant

#### Standards

European directive WEEE concerned

#### Safety

Protection index IP IP31

#### Use conditions

Operating temperature -10 ... 40 °C

#### temperatur

Ambient temperature 10 ... 40 °C