



S176-22X

Pet-tolerant IR detector local pictures

Product Datasheet

Connectivity

Connection mode radio TwinBand

Voltage

Operating voltage 4500 mV

Measurement

Detection Method Passive Infrared

Battery

life of battery 5 years

Camera

Shot recording Colour images that are sent by the transmitter via long-distance radio

Detection

Range of detection 12 m

Dimensions

Dimensions (LLxwxhh) 127 x 85 x 67 mm

Equipment

Angle of horizontal detection 60 °

Standards

European directive WEEE concerned

Safety

Protection index IP IP31

Use conditions

Operating temperature 0 ... 55 °C