



S144-22X

External pet-tolerant motion detector

Product Datasheet

Connectivity

Connection mode radio TwinBand

Voltage

Operating voltage 3 V DC

Measurement

Detection Method Passive Infrared

Battery

life of battery 4 years

Detection

Range of detection 12 m

Dimensions

Dimensions (LLxwxhh) 80 x 108 x 198 mm (sans brides)

Equipment

Angle of horizontal detection 90 °

Use

lense type Pet-tolerant

Standards

European directive WEEE concerned

Safety

Protection index IP IP54

Use conditions

Operating temperature -20 ... 50 °C

temperatur

Ambient temperature -20 ... 55 °C