



S121-22X

Wireless dual tech movement detector

Product Datasheet

Connectivity

Connection mode radio TwinBand

Main electrical features

Frequency 2,45 GHz

Voltage

Operating voltage 3600 mV

Measurement

Detection Method Bi-technology

Battery

life of battery 4 years

Detection

Range of detection 12 m

Dimensions

Dimensions (LLxwxh) 125 x 75 x 65 mm

Equipment

Angle of horizontal detection 90 °

Use

Lense type Volume

Standards

European directive WEEE concerned

Safety

Protection index IP IP31

Use conditions

Operating temperature -5 ... 55 °C

temperatur

Ambient temperature -5 ... 55 °C