



HXC011H

**Undervolt. Release 24V DC(h250...630)**

Product Datasheet

**Functions**

|                  |    |
|------------------|----|
| Delayed          | no |
| Switch-off delay | no |

**Voltage**

|                    |      |
|--------------------|------|
| DC control voltage | 24 V |
|--------------------|------|

**Power**

|                           |       |
|---------------------------|-------|
| Total power loss under IN | 0,6 W |
|---------------------------|-------|

**Standards**

|                                                              |            |
|--------------------------------------------------------------|------------|
| European directive WEEE                                      | concerned  |
| Product categories described in the W3E directive 2012/19/EU | Category 5 |

**Safety**

|                     |      |
|---------------------|------|
| Protection index IP | IP4X |
|---------------------|------|

**Use conditions**

|                                                          |        |
|----------------------------------------------------------|--------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3      |
| Altitude                                                 | 2000 m |