



HXF042H

Motor operator H1250-H1600 200-230VAC

Product Datasheet

Architecture

Type of order	motor drive
---------------	-------------

Main electrical features

Rated operational voltage Ue	200 / 230 V
Type of supply voltage	AC
Frequency	50/60 Hz

Voltage

Command voltage AC	200 / 230 V
--------------------	-------------

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	24 W
---------------------------	------

Standards

European directive RoHs	voluntary compliance
European directive WEEE	concerned

Safety

Protection index IP	IP4X
---------------------	------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m