



**slotted panel trunking BA7A 100x60, grey**

Technische Merkmale

**Architecture**

Flexible	no
----------	----

**Configuration**

Side wall configuration	Slotted
-------------------------	---------

Self-extinguishing	yes
--------------------	-----

**Electric current**

Current leak stable	yes
---------------------	-----

**Cover, door**

Lid shape	loose
-----------	-------

**Materials**

Colour	stone grey
--------	------------

Material	PVC
----------	-----

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

**Dimensions**

Trunking height	100 mm
-----------------	--------

Length	2000 mm
--------	---------

Trunking width	60 mm
----------------	-------

Slot width	6 mm
------------	------

Tongue width	6,5 mm
--------------	--------

**Installation, mounting**

Base punching	EN 50085-2-3:1999
---------------	-------------------

Fixing type	bottom punching
-------------	-----------------

**Cable**

Number of wires 1,5 mm <sup>2</sup> - 40% filling degree	198
--	-----

Internal/useful cross section	4988 mm <sup>2</sup>
-------------------------------	----------------------

Number of wires 2,5 mm <sup>2</sup> - 40% filling degree	142
--	-----

Number of wires 1,0 mm <sup>2</sup> - 40% filling degree	275
--	-----

**Scope of delivery**

Covers supplied with the product	yes
----------------------------------	-----

**Standards**

Approvals	EN50085-2-3
-----------	-------------

European directive RoHs	voluntary compliance
-------------------------	----------------------

UL 94 classification	V0
----------------------	----

BA7A100060

**Safety**

---

Halogen free	no
Fireproof classification	M1

---

**temperatur**

---

Ambient temperature	-5...60 °C
---------------------	------------

---