



BA7A100100

**slotted panel trunking BA7A 100x100, grey**

Technische Merkmale

**Architecture**

Flexible no

**Configuration**

Side wall configuration Slotted

Self-extinguishing yes

**Electric current**

Current leak stable yes

**Cover, door**

Lid shape loose

**Materials**

Colour stone grey

Material PVC

Material group plastic

Type of surface treatment untreated

**Dimensions**

Trunking height 100 mm

Length 2000 mm

Trunking width 100 mm

Slot width 6 mm

Tongue width 6,5 mm

**Installation, mounting**

Base punching EN 50085-2-3:1999

Fixing type bottom punching

**Cable**

Number of wires 1,5 mm<sup>2</sup> - 40% filling degree 346

Internal/useful cross section 8488 mm<sup>2</sup>

Number of wires 2,5 mm<sup>2</sup> - 40% filling degree 247

Number of wires 1,0 mm<sup>2</sup> - 40% filling degree 480

**Scope of delivery**

Covers supplied with the product yes

**Standards**

Approvals EN50085-2-3

European directive RoHs voluntary compliance

UL 94 classification V0

**Safety**

---

Halogen free	no
Fireproof classification	M1

---

**temperatur**

---

Ambient temperature	-5...60 °C
---------------------	------------

---