



HNG 50050/0 Grey 7035 Trunking

Technische Merkmale

Architecture

Flexible no

Configuration

Side wall configuration Slotted

Self-extinguishing yes

Electric current

Current leak stable yes

Cover, door

Lid shape loose

Materials

Colour light grey

RAL colour RAL 7035 - Light grey

Material PPO

Material group plastic

Type of surface treatment untreated

Dimensions

Trunking height 50 mm

Length 2000 mm

Trunking width 50 mm

Slot width 5 mm

Tongue width 7,5 mm

Installation, mounting

Base punching EN 50085-2-3:1999

Fixing type bottom punching

Cable

Number of wires 1,5 mm² - 40% filling degree 92

Internal/useful cross section 1974 mm²

Number of wires 2,5 mm² - 40% filling degree 66

Number of wires 1,0 mm² - 40% filling degree 128

Scope of delivery

Covers supplied with the product yes

Standards

European directive RoHs voluntary compliance

UL 94 classification V1

HNG5005007035B

Safety

Halogen free	yes
--------------	-----

temperatur

Ambient temperature	-25...90 °C
---------------------	-------------
