




LFF600657030



Flat corner LF60060, grey

Technische Merkmale

Architecture

Fixing mode Clipped

Functions

Overlapping yes

Suitable for functional integrity according to DIN 4102-12 no

Configuration

Antibacterial treatment no

Symmetrical yes

Cover, door

Lid with softlip No

Materials

Colour stone grey

RAL colour RAL 7030 - Stone grey

Material ABS

Type of surface treatment untreated

Dimensions

Trunking height 60 mm

Trunking width 57 mm

Measure a 95 mm

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Equipment

With protective film no

Standards

Approvals EN50085-2-1

Safety

Protection index IP IP30

Halogen free yes

Impact strength IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...60 °C
---------------------	------------
