




LFF600667030



End cap LF30060,40060,60060, grey

Technische Merkmale

Architecture

Fixing mode Clamping and screwable

Functions

Overlapping yes

Suitable for functional integrity according to DIN 4102-12 no

Configuration

Antibacterial treatment no

Connectivity

Trunking coupling without coupler

Materials

Colour stone grey

RAL colour RAL 7030 - Stone grey

Material PC-ABS

Material group plastic

Type of surface treatment untreated

Dimensions

Trunking height 60 mm

Trunking width 57 mm

Profile height 30-60 mm

Equipment

With protective film no

Standards

Approvals EN50085-2-1

European directive RoHs voluntary compliance

Safety

Halogen free yes

Impact strength IK07

Use conditions

Operating temperature -5...60 °C

temperatur

Ambient temperature -5...60 °C