



**T and X piece, LF 60060, grey**

Technische Merkmale

**Architecture**

Fixing mode Hold in position thanks to lid

**Functions**

Overlapping no  
 Suitable for functional integrity according to DIN 4102-12 no

**Configuration**

Antibacterial treatment no  
 Symetrical yes

**Cover, door**

Lid with softlip -

**Materials**

Colour stone grey  
 RAL colour RAL 7030 - Stone grey  
 Material PVC  
 Material group plastic  
 Type of surface treatment untreated

**Dimensions**

Trunking height 60 mm  
 Trunking width 57 mm  
 Measure a 170 mm

**Installation, mounting**

Base punching Without base punching

**Accessories included**

Accessory configuration Moulded

**Equipment**

With protective film no

**Standards**

European directive RoHs voluntary compliance

**Safety**

Halogen free no  
 Impact strength IK07

**Use conditions**

Operating temperature -5...60 °C

**temperatur**

---

Ambient temperature

-5...65 °C

---