



**Liféa trunking 60x90, c, 2 cable r., g**

Technische Merkmale

**Architecture**

Fixing mode bottom punched

**Functions**

Suitable for functional integrity according to DIN 4102-12 no

**Configuration**

Antibacterial treatment no

**Connectivity**

Trunking coupling Pre-equipped with couplers

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 23

**Cover, door**

Lid shape loose

**Materials**

Colour stone grey

RAL colour RAL 7030 - Stone grey

Material PVC

Material group plastic

Type of surface treatment untreated

Transparent no

**Dimensions**

Trunking height 60 mm

Length 2000 mm

Trunking width 90 mm

Distance bottom-punch along trunking-direction 125 mm

Distance bottom-punch crosswise trunking-direction 40 mm

**Cable**

Internal/useful cross section 4550 mm<sup>2</sup>

**Scope of delivery**

Delivery on roll no

LFF6009007030

**Equipment**

Number of plugable separators	1
Compartment quantity	1
Cable retainers per meter	2
Cable fixing clips included	yes
With protective film	no

**Standards**

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

**Safety**

Protection index IP	IP40
Halogen free	no
Impact strength	IK07

**Use conditions**

Operating temperature	-5...60 °C
-----------------------	------------