




M55257030



flat angle hal free LFxxx/FB 60x150 sg

Technische Merkmale

Architecture

Fixing mode Hold in position thanks to lid

Functions

Overlapping no
 Suitable for functional integrity according to DIN 4102-12 no

Configuration

Antibacterial treatment no
 Symmetrical yes

Compatibility

Product compatibility LF, LFF

Cover, door

Lid with softlip -

Materials

Colour stone grey
 RAL colour RAL 7030 - Stone grey
 Material PC-ABS
 Type of surface treatment untreated

Dimensions

Trunking height 61 mm
 Trunking width 150 mm
 Measure a 180 mm

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Equipment

With protective film no

Safety

Halogen free yes
 Impact strength IK07

Use conditions

Operating temperature -5...60 °C
