




M55367030



T and X piece, LF/FB 60190, grey

Technische Merkmale

Architecture

Fixing mode Hold in position thanks to lid

Functions

Overlapping no
Suitable for functional integrity according to DIN 4102-12 no

Configuration

Antibacterial treatment no
Symmetrical yes

Compatibility

Product compatibility LF, LFF, FB

Cover, door

Lid with softlip -

Materials

Colour stone grey
RAL colour RAL 7030 - Stone grey
Material PVC
Material group plastic
Type of surface treatment untreated

Dimensions

Trunking height 61 mm
Trunking width 190 mm
Measure a 290 mm

Installation, mounting

Base punching Without base punching

Accessories included

Accessory configuration Moulded

Equipment

With protective film no

Standards

Approvals EN50085-2-1
European directive RoHs voluntary compliance

Safety

Halogen free	no
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------
