




M55459010



Flat corner, LF/FB 60230, pure white

Technische Merkmale

Architecture

Fixing mode Hold in position thanks to lid

Functions

Overlapping no
 Suitable for functional integrity according to DIN 4102-12 no

Configuration

Antibacterial treatment no
 Symmetrical yes

Compatibility

Product compatibility LF, FB

Cover, door

Lid with softlip -

Materials

Colour pure white
 RAL colour RAL 9010 - Pure white
 Material PVC
 Type of surface treatment untreated

Dimensions

Trunking height 61 mm
 Trunking width 230 mm
 Measure a 260 mm

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Equipment

With protective film no

Safety

Halogen free no
 Impact strength IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...60 °C
---------------------	------------
