



VU36NE

Encl., Volta, flush, 3x12MOD, IP30

Technische Merkmale

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With a pipe-in lead	yes
---------------------	-----

Compatibility

Compatible with DIN rail mounting	yes
-----------------------------------	-----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Cover, door

Type of door closing	Latch
----------------------	-------

Identification of protection index	30
------------------------------------	----

Interlockable	no
---------------	----

Cover type	With Notch
------------	------------

Door locking	without
--------------	---------

Door leave	single
------------	--------

Door quantity	1
---------------	---

Cover type	Door
------------	------

Transparent cover or door	no
---------------------------	----

Materials

Colour	pure white
--------	------------

Colour	white
--------	-------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	plastic
----------	---------

Type of surface treatment	untreated
---------------------------	-----------

Dimensions

Insertion depth	89 mm
-----------------	-------

Depth of installed product	98 mm
----------------------------	-------

Internal depth	91,5 mm
----------------	---------

Height of installed product	630,5 mm
-----------------------------	----------

Installation height	595 mm
---------------------	--------

Length	630,5 mm
--------	----------

Width of installed product	348 mm
----------------------------	--------

Width in division units	12
-------------------------	----

Thickness of sidewall material	2,5 mm
--------------------------------	--------

Built-in height	615 mm
-----------------	--------

Built-in width	314,5 mm
----------------	----------

Installation, mounting

Suitable for outdoor use	no
--------------------------	----

Scope of delivery

With cover	no
------------	----

Accessories included

Mounting plate included	no
-------------------------	----

With lock	no
-----------	----

Equipment

Number of units	12
-----------------	----

Number of rows	3
----------------	---

Quantity of section in width	1
------------------------------	---

Quantity of rails	3
-------------------	---

Can be accessorized	yes
---------------------	-----

Extension possible	yes
--------------------	-----

Standards

GWT Glow wire test	650 °C
--------------------	--------

European directive WEEE	concerned
-------------------------	-----------

Protection class according to IEC-61140	II
---	----

Safety

IK protection code against mechanical impacts	IK07
---	------

Protection index IP	IP30
---------------------	------

Protection class	isol.class II
------------------	---------------

Halogen free	yes
--------------	-----

Impact strength	IK05
-----------------	------

Ultraviolet resistant	yes
-----------------------	-----

Use conditions

Operating temperature	-40...40 °C
-----------------------	-------------