



LS602

**Fuse carrier 2P 50A L51 acc. 3M**

Product Datasheet

**Architecture**

Number of poles	2 P
Type of pole	2 P

**Electric current**

Rated current	50 A
---------------	------

**Fuse**

CharactFuse	gG, aM
-------------	--------

**Power**

Total power loss under I <sub>N</sub>	12,5 W
---------------------------------------	--------

**Dimensions**

Depth of installed product	93 mm
Height of installed product	107 mm
Width of installed product	52,5 mm

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-5...40 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C