



G4773

H-distributor 1xplug 2xbuchs 3 pole Wago

Product Datasheet

Architecture

Number of poles	3 P
Type of pole	L PE N

Voltage

Max operating voltage	250 V
Rated surge voltage	4 kV

Electric current

Rated current	32 A
---------------	------

Power

Fire load	384 kJ
-----------	--------

Cover, door

Interlockable	yes
---------------	-----

Materials

Colour	black
Material	Mixed materials
Material group	mixed material
Type of surface treatment	untreated

Dimensions

Length	51 mm
Height	33 mm
Width	30 mm

Equipment

Number of outputs	2
Number of inputs	1
Contact Material	Copper
Mechanical coding	no

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Degree of contamination	3
Protection index IP	IP20
Halogen free	yes