



FWB62GS

**FWB encl., univers, IP44,950x550x161, QC**

Product Datasheet

**Architecture**

Fixing mode flush-mounting/surface-mounting/section make

**Configuration**

Module with terminals

**Compatibility**

Compatible with DIN rail mounting yes

**Electric current**

Rated current 125 A

**Cover, door**

Type of door closing hinged pattern handle

Number of keylock of the door 1

Cover type With Notch

Door leave single

Door quantity 1

Cover type Door

Transparent cover or door yes

**Materials**

Copper weight of the product 0,081 kg

Colour white

RAL colour RAL 9010 - Pure white

Material Steel

**Dimensions**

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 950 mm

Installation height 950 mm

Width of installed product 550 mm

Width in division units 12

**Installation, mounting**

Suitable for outdoor use no

**Accessories included**

Mounting plate included no

With lock no

**Equipment**

Number of rows	12
Quantity of section in width	2
Number of keys	1
Quantity of rails	12
Can be accessorized	yes
Extension possible	yes

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP44
Protection class	isol.class II