



ATA125058014

**Flat corner, ATEHA, 12x50, brown**

Product Datasheet

**Architecture**

Fixing mode Clipped

**Functions**

Overlapping yes

Suitable for functional integrity according to DIN 4102-12 no

**Configuration**

Antibacterial treatment no

Symetrical yes

**Cover, door**

Lid with softlip No

**Materials**

Colour brown

RAL colour RAL 8014 - Sepia brown

Material ABS

Type of surface treatment untreated

**Dimensions**

Trunking height 12 mm

Length 78 mm

Trunking width 50 mm

**Installation, mounting**

Base punching Without base punching

**Settings**

Angle range 90 °

**Accessories included**

Accessory configuration Moulded

**Equipment**

With protective film no

**Standards**

Approvals EN50085-2-1

**Safety**

Protection index IP IP40

Halogen free yes

Impact strength IK07

**Use conditions**

---

Operating temperature	-5...60 °C
-----------------------	------------

---

**temperatur**

---

Ambient temperature	-5...60 °C
---------------------	------------

---