



Trunking 20x50, L=2,0m, brown

Product Datasheet

Architecture

Fixing mode bottom punched

Functions

Suitable for functional integrity according to DIN 4102-12 no

Configuration

Antibacterial treatment no

Connectivity

Trunking coupling without coupler

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 3

Maximum number of cables (Ø 11 mm, 50% fill) 3

Cover, door

Lid shape premounted

Materials

Colour brown

RAL colour RAL 8014 - Sepia brown

Material PVC

Material group plastic

Type of surface treatment untreated

Transparent no

Dimensions

Trunking height 20 mm

Length 2000 mm

Trunking width 52 mm

Cable

Number of wires 1,5 mm² - 40% filling degree 61

Internal/useful cross section 900 mm²

Number of wires 2,5 mm² - 40% filling degree 45

Scope of delivery

Delivery on roll no

ATA205028014

Equipment

| | |
|-----------------------------|-----|
| Number of fix dividers | 2 |
| Cable retainers per meter | 2 |
| Cable fixing clips included | yes |
| With protective film | no |

Standards

| | |
|-------------------------|----------------------|
| Approvals | EN50085-2-1 |
| European directive RoHs | voluntary compliance |

Safety

| | |
|---------------------|------|
| Protection index IP | IP40 |
| Halogen free | no |
| Impact strength | IK07 |

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...65 °C |
|-----------------------|------------|