


SL201151



Trunking base SL20115 black

Product Datasheet

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	9
Cable capacity 11 mm D e.g. NYM 3 x 1.5mm ² 1st chamber	1 Part
Cable capacity 11 mm D e.g. NYM 3 x 1.5mm ² 2nd chamber	2 Part
Cable capacity 11 mm D e.g. NYM 3 x 1.5mm ² 3rd chamber	5 Part
Cable capacity 11 mm D e.g. NYM 3 x 1.5mm ² 4. chamber	5 Part

Materials

Colour	black
Material	PVC
Material group	plastic

Dimensions

Trunking height	115 mm
Length	2000 mm
Trunking width	20 mm

Cable

Number of wires 1,5 mm ² - 40% filling degree	129
Number of wires 2,5 mm ² - 40% filling degree	85

Equipment

Number of fix dividers	3
Compartment quantity	4
With carpet border	no
With protective film	no

Standards

Approvals	CE
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP40
Halogen free	no
Impact strength	IK07

Use conditions

Operating temperature	5...60 °C
-----------------------	-----------

temperatur

Ambient temperature	5...60 °C
---------------------	-----------