




SL20080911D1



acc.box univ. SL20080 alu

Product Datasheet

Architecture

Fixing mode Clamping and screwable

Configuration

Antibacterial treatment no
Empty housing no

Compatibility

Device installation compatible format Standard 60mm

Materials

Colour aluminium
Colour aluminium optics
Material plastic
Material group mixed material
Type of surface treatment Painted

Dimensions

Depth of installed product 48 mm
Height of installed product 171 mm
Trunking height 80 mm
Length 102 mm
Trunking width 20 mm
Format overhanging wiring accessory

Installation, mounting

Mounting way horizontal

Accessories included

Fitted with empty

Equipment

Number of units 1

Standards

Approvals CE
European directive RoHs voluntary compliance

Safety

Protection index IP IP40
Halogen free yes
Impact strength IK07

Use conditions

Operating temperature	5...60 °C
-----------------------	-----------

temperatur

Ambient temperature	5...60 °C
---------------------	-----------
