


# h3 ACBs

Air Circuit Breakers are used to protect low voltage installations from 800 to 6300A. These devices feature a high level of performance in a reduced volume.





HXA001H

## Accessories

Description	Pack Qty.	Art No.
Shunt trip 24V DC (x160-P160-x250-P250)	1	HXA001H
Shunt trip 48V DC (x160-P160-x250-P250)	1	HXA002H
SHT 100-120V AC (x160-P160-x250-P250)	1	HXA003H
SHT 200-240V AC (x160-P160-x250-P250)	1	HXA004H
SHT 380-450V AC (x160-P160-x250-P250)	1	HXA005H
UVR 24V DC (x160-P160-x250-P250)	1	HXA011H
UVR 100-120V AC (x160-P160-x250-P250)	1	HXA013H
UVR 200-240V AC (x160-P160-x250-P250)	1	HXA014H
UVR 380-450V AC (x160-P160-x250-P250)	1	HXA015H
AX contact 1NO+NC 250VAC (x/P160-x/P250)	1	HXA021H
AL contact 1NO+NC 250VAC (x/P160-x/P250)	1	HXA024H
AX low lvl. 1NO+NC 125VAC(x/P160-x/P250)	1	HXA025H
AL low lvl. 1NO+NC 125VAC(x/P160-x/P250)	1	HXA026H
Direct rotary handle x160	1	HXA030H
Extended rotary handle x160	1	HXA031H
Padlock (x160-P160-x250-P250)	1	HXA039H
UVR delayed 380-450V AC (x/P160-x/P250)	1	HXA055H
Direct rotary handle x250	1	HXB030H
Extended rotary handle x250	1	HXB031H
Motor operator x250 24V DC	1	HXB040H
Motor operator x250 230-240VAC	1	HXB042H
Interlocking wire type x250	1	HXB065H
Interlock front cover x250	1	HXB066H
Elec. interlock Motor A (x/P/h 250)	1	HXB068H
Elec.interlock MotB(x/P/h250-h400..1000)	1	HXB069H
Interlock cable 1m(P160-x/h/P250..1000)	1	HXB070H
Interlock cable 1.5m(P160-x/h250..1000)	1	HXB071H
Shunt trip Release 24V DC(h250...1000)	1	HXC001H
Shunt trip Release 48V DC(h250...1000)	1	HXC002H
SHT trip Release 100-120VAC(h250...1000)	1	HXC003H
SHT trip Release 200-240VAC(h250...1000)	1	HXC004H
SHT trip Release 380-450VAC(h250...1000)	1	HXC005H
Shunt trip Release 110V DC(h250...1000)	1	HXC008H
Undervolt. Release 24V DC(h250...630)	1	HXC011H
Undervolt. Release 100-120VAC(h250..630)	1	HXC013H
Undervolt. Release 200-240VAC(h250..630)	1	HXC014H
Undervolt. Release 380-450VAC(h250..630)	1	HXC015H
Undervolt. Release 100-120VDC(h250..630)	1	HXC018H
Undervolt. Release 200-240VDC(h250..630)	1	HXC019H
AX contact 1NO+1NC 230VAC(h250...1600)	1	HXC021H
Alarm contact 1NO+1NC 230V(h250...1600)	1	HXC024H
Aux low lvl 1NO+NC 125V AC(h250...1600)	1	HXC025H
AL contact low level 1NO+NC(h250...1600)	1	HXC026H
Direct rotary handle H250	1	HXC030H
Extended rotary handle H250	1	HXC031H
Padlock H250	1	HXC039H
Motor operator h250 24V DC	1	HXC040H
Motor operator H250 230-240VAC	1	HXC042H
UVR delayed h250-h630 24V DC	1	HXC051H
UVR delayed h250-h630 110-120V AC	1	HXC053H
UVR delayed h250-h630 220-240V AC	1	HXC054H
UVR delayed h250-h630 380-415V AC	1	HXC055H
Interlocking wire type H250	1	HXC065H
Interlock front cover h250	1	HXC066H
Direct rotary handle H400-H630	1	HXD030H
Extended rotary handle H400-H630	1	HXD031H
Padlock h400-h1000	1	HXD039H
Motor operator h400-h630 24-48V DC	1	HXD040H
Motor operator H400-H630 100-240VAC	1	HXD042H
UVR delayed h400-h630 4P 24VDC	1	HXD051H
UVR delayed h400-h630 4P 110-120VAC	1	HXD053H
UVR delayed h400-h630 4P 220-240VAC	1	HXD054H
UVR delayed h400-h630 4P 380-415VAC	1	HXD055H
Interlocking wire type H400-H630	1	HXD065H
Interlock front cover h630	1	HXD066H
Elec. interlock for Motor A (h400 1000)	1	HXD068H

Description	Pack Qty.	Art No.
UVR 24VDC (h800-h1000-h1600)	1	HXE011H
UVR 110-120VAC (h800-h1000-h1600)	1	HXE013H
UVR 220-240VAC (h800-h1000-h1600)	1	HXE014H
UVR 380-415VAC (h800-h1000-h1600)	1	HXE015H
UVR 100-120 V DC (h800-h1000-h1600)	1	HXE018H
UVR 200-240 V DC (h800-h1000-h1600)	1	HXE019H
Direct rotary handle H800-H1000	1	HXE030H
Extended rotary handle H800-H1000	1	HXE031H
Motor operator h800-h1000 24-48V DC	1	HXE040H
Motor operator H800-H1000 100-240VAC	1	HXE042H
UVR delayed h800-h1600 3P 24VDC	1	HXE051H
UVR delayed h800-h1600 3P 110-120VAC	1	HXE053H
UVR delayed h800-h1600 3P 220-240VAC	1	HXE054H
UVR delayed h800-h1600 3P 380-415VAC	1	HXE055H
Interlocking wire type H800-H1000	1	HXE065H
Interlock front cover h1000	1	HXE066H
Direct rotary handle H1250-H1600	1	HXF030H
Extended rotary handle H1250-H1600	1	HXF031H
Padlock H1250-H1600	1	HXF039H
Motor operator h1250-h1600 24V DC	1	HXF040H
Motor operator H1250-H1600 200-230VAC	1	HXF042H
UVR delayed h800-h1600 4P 24VDC	1	HXF051H
UVR delayed h800-h1600 4P 110-120VAC	1	HXF053H
UVR delayed h800-h1600 4P 220-240VAC	1	HXF054H
UVR delayed h800-h1600 4P 380-415VAC	1	HXF055H