

HRC cartridge fuses



LF300G

gG type

Description	Pack	Art No.
Industrial fuse-links 10x38 gG 0.5A	10	LF300G
Industrial fuse-links 10x38 gG 1A	10	LF301G
Industrial fuse-links 10x38 gG 2A	10	LF302G
Industrial fuse-links 10x38 gG 4A	10	LF304G
Industrial fuse-links 10x38 gG 6A	10	LF306G
Industrial fuse-links 10x38 gG 8A	10	LF308G
Industrial fuse-links 10x38 gG 10A	10	LF310G
Industrial fuse-links 10x38 gG 12A	10	LF312G
Industrial fuse-links 10x38 gG 16A	10	LF316G
Industrial fuse-links 10x38 gG20A	10	LF320G
Industrial fuse-links 10x38 gG25A	10	LF325G
Industrial fuse-links 10x38 gG 32A	10	LF332G
Industrial fuse-links 14x51 gG 2A	10	LF402G
Industrial fuse-links 14x51 gG 4A	10	LF404G
Industrial fuse-links 14x51 gG 6A	10	LF406G
Industrial fuse-links 14x51 gG 8A	10	LF408G
Industrial fuse-links 14x51 gG 10A	10	LF410G
Industrial fuse-links 14x51 gG 12A	10	LF412G
Industrial fuse-links 14x51 gG 16A	10	LF416G
Industrial fuse-links 14x51 gG 20A	10	LF420G
Industrial fuse-links 14x51 gG 25A	10	LF425G
Industrial fuse-links 14x51 gG 32A	10	LF432G
Industrial fuse-links 14x51 gG 40A	10	LF440G
Industrial fuse-links 14x51 gG 45A	10	LF445G
Industrial fuse-links 14x51 gG 50A	10	LF450G
Industrial fuse-links 22x58 gG 16A	10	LF516G
Industrial fuse-links 22x58 gG 20A	10	LF520G
Industrial fuse-links 22x58 gG 25A	10	LF525G
Industrial fuse-links 22x58 gG 32A	10	LF532G
Industrial fuse-links 22x58 gG 40A	10	LF540G
Industrial fuse-links 22x58 gG 50A	10	LF550G
Industrial fuse-links 22x58 gG 63A	10	LF563G
Industrial fuse-links 22x58 gG 80A	10	LF580G
Industrial fuse-links 22x58 gG 100A	10	LF590G
Industrial fuse-links 22x58 gG 125A	10	LF599G



LF300M

aM type

Description	Pack	Art No.
Industrial fuse-links 10x38 aM 0,5A	10	LF300M
Industrial fuse-links 10x38 aM 1A	10	LF301M
Industrial fuse-links 10x38 aM 2A	10	LF302M
Industrial fuse-links 10x38 aM 4A	10	LF304M
Industrial fuse-links 10x38 aM 6A	10	LF306M
Industrial fuse-links 10x38 aM 8A	10	LF308M
Industrial fuse-links 10x38 aM 10A	10	LF310M
Industrial fuse-links 10x38 aM 12A	10	LF312M
Industrial fuse-links 10x38 aM 16A	10	LF316M
Industrial fuse-links 10x38 aM 20A	10	LF320M
Industrial fuse-links 10x38 aM 25A	10	LF325M
Industrial fuse-links 10x38 aM 32A	10	LF332M
Industrial fuse-links 14x51 aM 2A	10	LF402M
Industrial fuse-links 14x51 aM 4A	10	LF404M
Industrial fuse-links 14x51 aM 6A	10	LF406M
Industrial fuse-links 14x51 aM 8A	10	LF408M
Industrial fuse-links 14x51 aM 10A	10	LF410M
Industrial fuse-links 14x51 aM 12A	10	LF412M
Industrial fuse-links 14x51 aM 16A	10	LF416M
Industrial fuse-links 14x51 aM 20A	10	LF420M
Industrial fuse-links 14x51 aM 25A	10	LF425M
Industrial fuse-links 14x51 aM 32A	10	LF432M
Industrial fuse-links 14x51 aM 40A	10	LF440M
Industrial fuse-links 14x51 aM 45A	10	LF445M
Industrial fuse-links 14x51 aM 50A	10	LF450M
Industrial fuse-links 22x58 aM 16A	10	LF516M
Industrial fuse-links 22x58 aM 20A	10	LF520M
Industrial fuse-links 22x58 aM 25A	10	LF525M
Industrial fuse-links 22x58 aM 32A	10	LF532M
Industrial fuse-links 22x58 aM 40A	10	LF540M
Industrial fuse-links 22x58 aM 50A	10	LF550M
Industrial fuse-links 22x58 aM 63A	10	LF563M
Industrial fuse-links 22x58 aM 80A	10	LF580M
Industrial fuse-links 22x58 aM 100A	10	LF590M
Industrial fuse-links 22x58 aM 125A	10	LF599M