



HHS025DC

h3+ MCCBs P160 TM 25kA

Description	Pack qty.	Art No.
MCCB h3+ P160 TM 3x25A 25kA	1	HHS025DC
MCCB h3+ P160 TM 4x25A 25kA	1	HHS026DC
MCCB h3+ P160 TM 3x40A 25kA	1	HHS040DC
MCCB h3+ P160 TM 4x40A 25kA	1	HHS041DC
MCCB h3+ P160 TM 3x63A 25kA	1	HHS063DC
MCCB h3+ P160 TM 4x63A 25kA	1	HHS064DC
MCCB h3+ P160 TM 3x80A 25kA	1	HHS080DC
MCCB h3+ P160 TM 4x80A 25kA	1	HHS081DC
MCCB h3+ P160 TM 3x100A 25kA	1	HHS100DC
MCCB h3+ P160 TM 4x100A 25kA	1	HHS101DC
MCCB h3+ P160 TM 3x125A 25kA	1	HHS125DC
MCCB h3+ P160 TM 4x125A 25kA	1	HHS126DC
MCCB h3+ P160 TM 3x160A 25kA	1	HHS160DC
MCCB h3+ P160 TM 4x160A 25kA	1	HHS161DC



HMS025DC

h3+ MCCBs P160 TM 50kA

Description	Pack qty.	Art No.
MCCB h3+ P160 TM 3x25A 50kA	1	HMS025DC
MCCB h3+ P160 TM 4x25A 50kA	1	HMS026DC
MCCB h3+ P160 TM 3x40A 50kA	1	HMS040DC
MCCB h3+ P160 TM 4x40A 50kA	1	HMS041DC
MCCB h3+ P160 TM 3x63A 50kA	1	HMS063DC
MCCB h3+ P160 TM 4x63A 50kA	1	HMS064DC
MCCB h3+ P160 TM 3x80A 50kA	1	HMS080DC
MCCB h3+ P160 TM 4x80A 50kA	1	HMS081DC
MCCB h3+ P160 TM 3x100A 50kA	1	HMS100DC
MCCB h3+ P160 TM 4x100A 50kA	1	HMS101DC
MCCB h3+ P160 TM 3x125A 50kA	1	HMS125DC
MCCB h3+ P160 TM 4x125A 50kA	1	HMS126DC
MCCB h3+ P160 TM 3x160A 50kA	1	HMS160DC
MCCB h3+ P160 TM 4x160A 50kA	1	HMS161DC



HES025DC

h3+ MCCBs P160 TM 70kA

Description	Pack qty.	Art No.
MCCB h3+ P160 TM 3x25A 70kA	1	HES025DC
MCCB h3+ P160 TM 4x25A 70kA	1	HES026DC
MCCB h3+ P160 TM 3x40A 70kA	1	HES040DC
MCCB h3+ P160 TM 4x40A 70kA	1	HES041DC
MCCB h3+ P160 TM 3x63A 70kA	1	HES063DC
MCCB h3+ P160 TM 4x63A 70kA	1	HES064DC
MCCB h3+ P160 TM 3x80A 70kA	1	HES080DC
MCCB h3+ P160 TM 4x80A 70kA	1	HES081DC
MCCB h3+ P160 TM 3x100A 70kA	1	HES100DC
MCCB h3+ P160 TM 4x100A 70kA	1	HES101DC
MCCB h3+ P160 TM 3x125A 70kA	1	HES125DC
MCCB h3+ P160 TM 4x125A 70kA	1	HES126DC
MCCB h3+ P160 TM 3x160A 70kA	1	HES160DC
MCCB h3+ P160 TM 4x160A 70kA	1	HES161DC