



80164785



IP20

easy

S/B-KNXPB.4g.8PB.KNX-TP+EASY.FPL.al/anth

Technische Merkmale

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With room temperature controller	no
----------------------------------	----

- operating concept "independent push-button" function predefined
- operating concept for "roller shutter/blind" function predefined
- switching of scenes (1..8) possible
- Orientation LED can be controlled via object
- brightness value of the status LED for day/nighttime operation preset, status LED for day/nighttime operation can be controlled via object
- integrated temperature sensor with output of the measured values
- Colour of status LED uniformly adjustable for complete device
- push-button functions: including switching, dimming, roller shutter/blind, timer, priority, temperature setpoint adjustment, operating mode changeover
- Function for manual interruption of automatic functions already triggered
- operating surfaces as buttons (single-surface operation) and rockers (two-surface operation)
- the brightness of status LEDs are individually adjustable for button/ rocker function
- brightness value of the status LEDs for day/nighttime operation adjustable via object or manually
- value transmitter for dimming, position, brightness temperature values 1 and 2 byte
- button/rocker functions for switching, dimming, roller shutter/blind, value transmitter 1/2 byte, room thermostat extension unit, priority, scene, automatic control deactivation
- integrated temperature sensor with output of the measured values via object
- button functions for switching, dimming, roller shutter/blind, timer, value transmitter 1/2 byte, room thermostat extension unit, priority, scene, 2-channel mode, step switch, automatic control deactivation
- rocker functions for switching, dimming, roller shutter/blind, value transmitter 1/2 byte, room thermostat extension unit, priority, scene, 2-channel mode, automatic control deactivation
- parameter defineable lock function
- 3-step switch, function for incremental selection of up to 7 stored values
- Status LED configurable in its colour per button

Compatibility

- extension unit for light scene push-button

Controls and indicators

With LED indication	yes
Number of buttons	4
- operating areas configurable as one or two-area operation	

Electric current

Bus current consumption (data transfer)	max. 20 mA
---	------------

Power

Power consumption, KNX	≈ 150 mW
------------------------	----------

Measurement

- value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display	no
--------------	----

Materials

Colour of design line	aluminium/anthracite
Colour independent of design lines	for anthracite and aluminium
Colour	aluminium/anthracite
RAL colour	RAL 7016 - Anthracite grey
Material	thermoplastic
Material for printing	Paper
Surface appearance	glossy
Type of surface treatment	untreated
Material family	Plastic

Dimensions

Labelling field length (W x H)	52,3 x 24,9 mm
Height	55,3 mm
Width	55,8 mm

LED control

LED	with white operating LED, with 2 RGB status LEDs per rocker
-----	---

Connection

- for bus coupling unit flush-mounted

Settings

Supported configuration modes	system, easy
- single and two push-button operation parameterisable	

Scope of delivery

Bus connection included	no
-------------------------	----

Accessories included

Inscribable, with labelling field	yes
-----------------------------------	-----

Equipment

Number of actuation points	8
With anti-theft/dismantling protection	yes
Product type:	product type: push-button 4gang

Use

Differentiation characteristic 1 - Sales	with labelling fields
Differentiation characteristic 2 - Sales	and RGB LED
Differentiation characteristic 3 - Sales	with integrated temperature sensor

Safety

Protection index IP	IP20
Halogen free	no
- with dismantling protection	
- alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte	

Use conditions

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C (storage at > 45°C reduces the service life)
- integrated temperature sensor with output of the measured values via object	

Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker S.1/B.3/B.7
Secondary design line(s)	KNX, Berker S.1, Berker B.3, Berker B.7

Instructions

- Use only in conjunction with bus coupling unit 8004 00 01!
- In the design lines S.1/B.x and K.x only to be used in combination with a frame with a large cut-out!