



85655229



IP20

HBNet FW 1k Q1 P-W GLÄ

Technische Merkmale

Functions

- ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value
- reset function (to factory setting)
- easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control
- quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

Controls and indicators

- operating areas configurable as one or two-area operation
- with configuration button

Connectivity

Radio protocol	KNX Radio
Receiver category	2

Frequency

Radio transmission frequency	868,3 MHz
------------------------------	-----------

Power

Radio transmission power	< 10 mW
--------------------------	---------

Measurement

Relative humidity (without condensation)	0...65 % (without condensation)
--	---------------------------------

Battery

Battery service life [years]	≈ 5
- with lithium coin cell battery 3 V type: CR 2430	

Materials

Colour of design line	polar white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	velvety

Dimensions

Assembling height	14 mm
-------------------	-------

LED control

LED	with transmission status and battery status LED, red/green/orange, with configuration LED
-----	---

Installation, mounting

Installation mode	for flat surface mounting and extension of combinations
-------------------	---

Connection

- integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system

Settings

- toolless quicklink configuration using buttons and LED display
- top and bottom operating area are freely configurable

Equipment

Number of radio channels	2
Number of quicklink links	max. 20 transmitter/receiver
Transmitter duty cycle	1 %

Safety

- with dismantling protection

Use conditions

Operating temperature	-5...45 °C
- low intrinsic energy requirement	

Identification

Application, usage	KNX radio- operating systems
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9