



FZ021N

## Door, univers, right, f.encl. 1100x300mm

Product Datasheet

### Architecture

|                        |       |
|------------------------|-------|
| Intended door position | right |
|------------------------|-------|

### Configuration

|   |    |
|---|----|
| Version as door for disconnecting switch interlocking | no |
|---|----|

### Cover, door

|                                   |                                       |
|-----------------------------------|---------------------------------------|
| Type of door closing              | Hinged pattern handle and bar locking |
| Number of keylock of the door     | 1                                     |
| Door type for switch gear cabinet | Partial door                          |
| Door quantity                     | 1                                     |
| Transparent cover or door         | no                                    |

### Materials

|                           |                       |
|---------------------------|-----------------------|
| Colour                    | pure white            |
| Colour                    | white                 |
| RAL colour                | RAL 9010 - Pure white |
| Material                  | sheet steel           |
| Type of surface treatment | powder-coated         |

### Dimensions

|                             |         |
|-----------------------------|---------|
| Depth of installed product  | 12 mm   |
| Internal depth              | 92 mm   |
| Height of installed product | 1069 mm |
| Width of installed product  | 269 mm  |

### Equipment

|                              |   |
|------------------------------|---|
| Number of rows               | 7 |
| Quantity of section in width | 1 |
| Number of keys               | 1 |

### Standards

|                         |               |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

### Safety

|                     |      |
|---------------------|------|
| Protection index IP | IP44 |
|---------------------|------|

