



VS108TJ



VS108TJ1

**Sm.distr, golf, surface, 8M, transp. door**

Product Datasheet

#### Architecture

Fixing mode	surface-mounting
-------------	------------------

#### Functions

With a pipe-in lead	yes
---------------------	-----

#### Compatibility

Compatible with DIN rail mounting	yes
-----------------------------------	-----

#### Main electrical features

Nominal voltage	400 V
-----------------	-------

#### Electric current

Rated current	63 A
---------------	------

#### Cover, door

Type of door closing	Latch
----------------------	-------

Identification od protection index	40
------------------------------------	----

Interlockable	no
---------------	----

Cover type	Closed (plain)
------------	----------------

Door locking	without
--------------	---------

Door leave	single
------------	--------

Door quantity	1
---------------	---

Cover type	Door
------------	------

Transparent cover or door	yes
---------------------------	-----

#### Materials

Colour	pure white
--------	------------

Colour	white
--------	-------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	plastic
----------	---------

Type of surface treatment	untreated
---------------------------	-----------

#### Dimensions

Depth of installed product	99 mm
----------------------------	-------

Internal depth	99 mm
----------------	-------

Height of installed product	184 mm
-----------------------------	--------

Width of installed product	210 mm
----------------------------	--------

Width in division units	8
-------------------------	---

#### Installation, mounting

Suitable for outdoor use	no
--------------------------	----

## Accessories included

Mounting plate included	no
With lock	no

## Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	yes
Extension possible	yes

## Standards

GWT Glow wire test	650 °C
European directive WEEE	concerned

## Safety

IK protection code against mechanical impacts	07
Protection class	isol.class II
Halogen free	yes
Ultraviolet resistant	no

## Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------