



HED400H

MCCB h630 3P 70kA 400A LSI

Product Datasheet

Architecture

Type of order	Toggle
Number of poles	3 P
Type of pole	3P3D

Functions

Complete device with protection unit	yes
Trip Unit	LSI
Integrated earth fault protection	no

Compatibility

Compatible with DIN rail mounting	no
-----------------------------------	----

Main electrical features

Frequency	50/60 Hz
Rated operational voltage Ue	220/690 V

Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V
With under voltage release	no

Electric current

Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	70 kA
Rated service breaking capacity Ics AC according IEC 60947-2	71 %
Breaking capacity on 1 pole with 230 V NF 60947-2	60 kA
Breaking capacity on 1 pole with 400 V NF 60947-2	9 kA
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 440V AC IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	20 kA
Thermal protection nob setting xIN	0,4/0,5/0,63/0,8/0,9/0,95/1

Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

Power

Power loss per pole at In	20,8 W
Total power loss under IN	62,4 W

Tripping

Tripmode	LSI
Thermal protection trip time	5/10/11/19/21/29 ms
Time of response when opening	10 ms

Electrical specifications

Magnetic trip delay time	100 to 200 ms
--------------------------	---------------

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

Installation, mounting

Tightening torque	22Nm
DIN rail mounting with optional adaptator	no

Connection

Connection cross-sect. rigid cable	35 / 240mm ²
Connection cross-sect. flexible conductor	35 / 240mm ²
Connection	Front connection
Type of connection	Terminal

Settings

Magnetic protection nob setting xIN	2,5/5/10
Setting type In or Ith	IrTh
Range of the magnetic adjustment	2240/2800/3500/4480/5040/5200/5200 A

Equipment

Motor drive optional	yes
----------------------	-----

Use cases

Category of use	A
-----------------	---

Standards

Standard text	IEC 60947-2
European directive WEEE	concerned

Safety

Protection index IP	IP4X
---------------------	------

Use conditions

Altitude	2000 m
Storage temperature	-35 to 70 °C
Air humidity protection	for all climates
